

Cut-protective chemical-resistant gloves with high-visibility liner, for advanced protection

- **Specialized protection:** AlphaTec® 58-735 chemical gloves' nitrile barrier protects against common chemicals
- **Enhanced features:** Their high-visibility inner liner indicates when the shell is compromised, warning users, while their foldable cuff can prevent chemicals running down the arm
- **Heightened defenses:** AlphaTec® 58-735 safety gloves' INTERCEPT™ Cut Resistance knitwork ensures ANSI A3/EN ISO C cut protection
- **Tightened grip:** ANSELL GRIP™ nitrile shell treatment delivers better grip for handling both wet and oily components
- **Optimized durability:** AlphaTec® 58-735 PPE gloves also achieve ANSI level 6 abrasion resistance, for longer wear
- **Elevated comfort and dexterity:** The liner's integration into the nitrile shell ensures better fit, comfort and tactility
- **Harm-free food handling:** These AlphaTec® gloves comply with EU and FDA food handling regulations, while Oeko-Tex® Standard 100 approval certifies them free of substances considered harmful to human health

Industries

- Automotive
- Chemical
- Life Sciences
- Machinery and Equipment
- Oil and gas
- Food Processing
- Metal fabrication
- Emergency Medical Services

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Filling, blending and charging of raw materials
- Sample taking and processing
- Removal of broken glassware
- Spill or leakage cleanup
- Assembling and mounting components
- Mixing or loading chemicals
- Cleaning of plant and machines
- Handling application & cleaning tools



Key Features

- **Nitrile shell barrier:** EN 374 Type A resistance against common chemicals
- **High-visibility inner liner:** Indicates when cut, for superior safety
- **INTERCEPT™ Cut Resistance Technology:** ANSI A3/EN ISO C cut protection

Technologies



ANSELL GRIP™

Ansell Grip Technology



INTERCEPT™

Cut Resistance Technology



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-735	Ansell INTERCEPT™ Technology, Nitrile, ANSELL GRIP™	18	6, 7, 8, 9, 10, 11	350 mm / 13.8 inches	Green	• 6 pairs/bag; 12 bags/case

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.