



HardCap A1+™

Hi-Vis Baseball Style Bump Cap with HDPE Protective Liner and Adjustable Back

- Ultra sleek design means the HardCap A1+™ is almost indistinguishable from a low-profile baseball cap
- The protective HDPE liner is removable, so the outer cap is fully washable with a plastic brim
- Unique size adjuster slides on an elastic strip to give a quick, secure fit. Angled downward to fit under nape of neck
- Terry cloth sweatband adds comfort and absorption for the wearer
- Reflective piping adds extra visibility and therefore safety in all working environments
- Holes in the liner match up with two mesh panels on the cap to provide added ventilation for coolness and comfort

Applications

- Assembly Line
- Maintenance
- Aviation
- Automotive Applications

Technical Data

Color	Hi-Vis Orange
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	22.24 x 14.96 x 13.19
Case Weight (lbs)	11.09
Country of Origin	China
Shell Material	--
Shell	Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Elastic Strap
Sweatband	Terry Cloth
Construction	--
Certifications	--
Product Circularity	--

Care Instructions



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
282-ABR170-OR	Hi-Vis Orange	OS	5038428136181	5038428136181	5038428136181