




Contempo™

Indirect Vent Goggle with Light Blue Body, Grey Lens and Anti-Scratch / Anti-Fog Coating

- Wraparound lens design with distortion-free panoramic viewing
- Offers indirect ventilation for liquid splash protection
- Wide facial flange for a secure seal
- Nose area split to fit the vast majority of users
- Clear blue transparent frame to prevent yellowing
- Fits comfortably over most prescription glasses
- Wide elastic headband with adjustable buckle
- Headband strap attaches to frame with a swivel clip to ensure a comfortable fit
- 6 Base curve lens
- Meets ANSI Z87.1
-  **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Protection from Liquid Splash, Dust and Light Impacts



Technical Data

Color	Light Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	50 Pair/Case
Case Dimensions (in)	18.11 x 9.06 x 20.67
Case Weight (lbs)	17.64
Country of Origin	Malaysia
Ventilation	Indirect
Headband	Elastic
Lens Color	Grey
Frame Material	PVC
Lens	Tinted
Lens Coating	Anti-Scratch, Anti-Fog
Base Curve	5.75
Construction	--
Certifications	ANSI Z87.1
Product Circularity	--

Care Instructions



SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
251-5300-000	Light Blue	Clear	Clear	AS	616314106293	01616314106292	02616314106291
251-5300-400	Light Blue	Clear	Clear	AS/AF	616314106309	01616314106308	02616314106307
251-5300-400-RHB	Light Blue	Clear	Clear	AS/AF	616314159558	01616314159557	02616314159556
251-5300-402	Light Blue	Tinted	Gray	AS/AF	616314106316	01616314106315	02616314106314

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated