



Whistler™

Cap Style Hard Hat with HDPE Shell, 4-Point Textile Suspension and Pin-Lock Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- Shell design includes a rain trough for extra convenience in adverse weather conditions
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- Precise height adjustment settings to ensure proper depth
- Low nape strap provides a secure fit, allowing the hard hat to stay on your head even when workers are looking down or bending over

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



Technical Data

Color	White, Yellow, Orange, Dark Green, Sky Blue, Navy, Gray, Black, Dark Gray, Red, Royal, Hi-Vis Orange, Hi-Vis Yellow, Gold, Northern Blue, Pink, Beige, Hi-Vis Red, Light Blue, Lime
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	--
Case Weight (lbs)	0.00
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Pin-Lock
Suspension	4 Point Nylon Webbing Cradle
Chin Strap	--
Sweatband	Felt Lined Foam
Construction	--
Certifications	ANSI/ISEA Z89.1, EN 397, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
CSA Type	--
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-22



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP241-10	Beige	OS	620606000107	10616314441094	10620606000104
280-HP241-11	Black	OS	620606000114	10620606000111	10620606000111
280-HP241-14	Dark Gray	OS	620606007021	10620606007028	10620606007028
280-HP241-04	Dark Green	OS	620606000046	10620606000043	10620606000043
280-HP241-13	Gold	OS	620606002422	10616314398848	10620606002429
280-HP241-09	Gray	OS	620606000091	10620606000098	10620606000098
280-HP241-31	Hi-Vis Orange	OS	620606002156	10620606002153	10620606002153
280-HP241-05	Hi-Vis Red	OS	620606000053	10616314441117	10620606000050
280-HP241-44	Hi-Vis Yellow	OS	620606002163	10620606002160	10620606002160
280-HP241-06	Light Blue	OS	620606000060	10616314366168	10620606000067
280-HP241-45	Lime	OS	620606004099	10616314372954	10620606004096
280-HP241-08	Navy	OS	620606000084	10616314366328	10620606000081
280-HP241-18	Northern Blue	OS	620606004211	10616314415057	10620606004218
280-HP241-03	Orange	OS	620606000039	10620606000036	10620606000036
280-HP241-20	Pink	OS	620606002149	10616314418959	10620606002146
280-HP241-15	Red	OS	620606000138	10620606000135	10620606000135
280-HP241-17	Royal	OS	620606000145	10620606000142	10620606000142
280-HP241-07	Sky Blue	OS	620606000077	10620606000074	10620606000074
280-HP241-01	White	OS	620606000015	10620606000012	10620606000012
280-HP241-02	Yellow	OS	620606000022	10620606000029	10620606000029