



NOVAX®

Class 00 Rubber Insulating Glove with Straight Cuff - 14"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Yellow
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 19.80
Case Weight (lbs)	12.59
Country of Origin	Malaysia
Material	Rubber
Length	14"
Cuff	Straight
Cuff Color	Yellow
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 00
------------------	----------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
170-00-14/7	Yellow	7	616314101649	01616314101648	02616314101647
170-00-14/8	Yellow	8	616314101656	01616314101655	02616314101654
170-00-14/9	Yellow	9	616314101663	01616314101662	02616314101661
170-00-14/10	Yellow	10	616314101618	01616314101617	02616314101616
170-00-14/11	Yellow	11	616314101625	01616314101624	02616314101623
170-00-14/12	Yellow	12	616314101632	01616314101631	02616314101630