



NOVAX®

Class 0 Rubber Insulating Glove with Straight Cuff - 14"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Yellow
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 19.80
Case Weight (lbs)	13.98
Country of Origin	Malaysia
Material	Rubber
Length	14"
Cuff	Straight
Cuff Color	Yellow
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 0
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
170-0-14/7	Yellow	7	616314101526	01616314101525	02616314101524
170-0-14/8	Yellow	8	616314101533	01616314101532	02616314101531
170-0-14/8.5	Yellow	8.5	616314436741	10616314436748	20616314436745
170-0-14/9	Yellow	9	616314101540	01616314101549	02616314101548
170-0-14/9.5	Yellow	9.5	616314436789	10616314436786	20616314436783
170-0-14/10	Yellow	10	616314101496	01616314101495	02616314101494
170-0-14/10.5	Yellow	10.5	616314789908	10616314789905	20616314789902
170-0-14/11	Yellow	11	616314101502	01616314101501	02616314101500
170-0-14/12	Yellow	12	616314101519	01616314101518	02616314101517