



AKLMNPST 2020

## Technical Data

Color	Orange
Sizes Available	S-2XL
Packaging	Pair Bagged Retail Ready
Packed	12 Dozen/Case
Case Dimensions (in)	13.39 x 12.60 x 18.90
Case Weight (lbs)	43.23
Country of Origin	Sri Lanka
Polymer	Latex
Thickness	28 Mil
Lining	Flocked
Length	12"
Cuff	Straight
Grip	Honeycomb
Dip	--
Construction	Unsupported
Certifications	Silicone Free
Product Circularity	--

## Assurance®

Unsupported Latex, Industrial Flock Lined with Honeycomb Grip - 28 Mil

- Heavy duty latex gloves provide extended wear and greater chemical resistance
- Provides resistance to acids, alkalis, alcohols, salts, ketones and animal fats
- Flock lined styles provide increased comfort and ease of donning
- Straight cuff adds additional strength
- Honeycomb pattern for an enhanced grip
- Chlorinated to harden and cleanse the surface of the glove

## Applications

- Food Processing
- Chemical Handling
- Chemical Refining
- Cleaning
- Janitorial

## Performance Data

ANSI Cut Level	--
EN 388	2020XX
EN 374-5	--

## Care Instructions



Do Not Wash



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
48-L302T/S	Orange	S	616314052194	01616314052193	02616314052192
48-L302T/M	Orange	M	616314034619	01616314034619	02616314034619
48-L302T/L	Orange	L	616314034602	01616314034602	02616314034602
48-L302T/XL	Orange	XL	616314034633	01616314034633	02616314034633
48-L302T/XXL	Orange	2XL	616314193842	01616314193841	02616314193840