



Technical Data

Color	Hi-Vis Orange, Hi-Vis Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	50/Case
Case Dimensions (in)	18.90 x 11.81 x 19.29
Case Weight (lbs)	38.58
Country of Origin	China
Clothing Type	Vests
Fabric	Mesh, Polyester
Reflective Type	Two-Tone
Reflective Width	2
Closure	Hook and Loop
Pocket Type	Internal Pocket, Chest Pocket
Construction	Self-Extinguishing
Certifications	ASTM D6413
Product Circularity	Reusable / Launderable

PIP®

ANSI Type R Class 2 Two-Tone Expandable FR Treated Mesh Vest

- Mesh polyester treated material to prevent after-flame
- Treatment good for up to 25 washes
- Adjustable sides for universal fit
- FR 2" two tone tape
- Hook and loop closure
- Not designed for use in an ARC flash or flash fire application
- Tested to ASTM D6413

Applications

- Road Work
- Survey Crews
- Shipyards
- Railyard
-

Performance Data

ANSI Type/Class	R2
-----------------	----

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-11



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
305-USV5FROR	Hi-Vis Orange	OS	616314088667	01616314088666	02616314088665
305-USV5FRLY	Hi-Vis Yellow	OS	616314073977	01616314073976	02616314073975