



## NOVAX®

### Class 0 Rubber Insulating Glove with Straight Cuff - 14"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

## Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

## Technical Data

Color	Black
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 19.80
Case Weight (lbs)	13.98
Country of Origin	Malaysia
Material	Rubber
Length	14"
Cuff	Straight
Cuff Color	Black
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

## Performance Data

Electrical Class	Class 0
------------------	---------

## Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
150-0-14/7	Black	7	616314066559	01616314066558	02616314066557
150-0-14/8	Black	8	616314066542	01616314066541	02616314066540
150-0-14/9	Black	9	616314066535	01616314066534	02616314066533
150-0-14/10	Black	10	616314066566	01616314066565	02616314066564
150-0-14/11	Black	11	616314066573	01616314066572	02616314066571
150-0-14/12	Black	12	616314066580	01616314066589	02616314066588