

Arc Visor Combination ATPVs:

Combination	Helmet		Visor(s)		Frame(s)		Chinguard		Earmuff		ATPV (cal/cm ²)
	PN	Description	PN	Description	PN	Description	PN	Description	PN	Description	
3	475358	V-Gard Cap (Med)	10115847	Arc Visor	10121267	elev temp, slotted cap, no debris control	X	X	X	X	11.7
5	10074067	Smooth Dome	10115847	Arc Visor	10121268	standard, universal cap, no debris control	X	X	X	X	12.0
7	475385	Topgard Cap	10115847	Arc Visor	10121267	elev temp, slotted cap, no debris control	X	X	X	X	12.1
8			10115847	Arc Visor	10121268	standard, universal cap, no debris control	X	X	X	X	12.8
10	475369	V-Gard Hat	10115858	Arc Visor, Nitro	10116627	standard, universal hat	10115828	retractable	X	X	18.0
11			10115847	Arc Visor	10116628	elev temp, universal hat	X	X	X	X	12.0
12	475358	V-Gard Cap (Med)	10115847	Arc Visor	10121268	standard, universal cap, no debris control	X	X	X	X	12.1
13			10115858	Arc Visor, Nitro	10121266	standard, slotted cap w/o debris control	10115827	standard	X	X	11.3
14			10115847	Arc Visor	10121266	standard, slotted cap w/o debris control	X	X	X	X	12.9
15	475369	V-Gard Hat	10115858	Arc Visor, Nitro	10154622	Slotted hat frame w/ debris control	10115827	Standard	X	X	19
16	475369	V-Gard Hat	10115847	Arc Visor	10154604	Slotted hat frame w/o debris control	X	X	X	X	14

Notes:

1 - All other combinations of the MSA V-Gard, Smooth Dome, Topgard, Thermalgard, and Skullgard caps and hats with any of the PNs below are rated to 11.0 cal/cm² based on the same visor, frame, and chinguard shape, type, and material as tested above:

10115858 AE Nitrometer Visor
 10115847 BF Visor
 10121266 standard, slotted, no debris control
 10121267 elev temp, slotted, no debris control
 10121268 standard, universal, no debris control
 10124426 elev temp, universal, no debris control
 10116627 standard, universal, for hats
 10116628 elev temp, universal, for hats
 10115827 standard chinguard
 10115828 retractable chinguard
 10115730 standard, slotted, w/ debris control
 10115821 elev temp, slotted, w/ debris control
 10115822 standard, universal, w/ debris control
 10116552 elev temp, universal, w/ debris control