



Caiman® Premium Split Deerskin MIG/Stick Welder's Glove with Fleece/Foam Insulation - 21" Length

- Industry first!... 21" glove length with heavy duty padding on the forearm and elbow for comfort
- Super supple black Genuine American Deerskin
- Gold split cowhide leather heat shield patch, reinforced palm, cuff and lean-on patch
- Sock lined foam/fleece insulated
- Patches, padding and reinforcements for comfort & protection
- Sewn with Kevlar® thread
- Exclusive 3-Dimensional, pre-curved fingers, and form-fitting design for ultimate fit, comfort & dexterity
- Complimentary 3" carabiner to keep gloves together with exclusive Caiman® loops on each pair
- This style is also available in a Left Hand Only option... 1878-0 for Large and 1878-1 for XL
- **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov



Technical Data

Color	Gold
Sizes Available	L-XL
Packaging	Pair Tagged Retail Ready
Packed	36 Pair/Case
Case Dimensions (in)	23.23 x 14.57 x 22.44
Case Weight (lbs)	46.30
Country of Origin	China
Hide	Split Deerskin
Grade	Premium
Cuff	Gauntlet
Length	21"
Palm	Reinforced
Back	Full Leather
Closure	Pull-Strap
Thumb	Keystone
Stitching	Kevlar
Construction	--
Certifications	--
Product Circularity	--

Performance Data

PPE Category	--
ARC Rating	cal/cm2
ANSI Cut Level	--
ANSI Puncture Level	--

Care Instructions



Do Not Wash



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
1878-5	Gold	L	710927187851	10710927187858	20710927187855
1878-6	Gold	XL	710927187868	10710927187865	20710927187862