

Skullgard® Protective Helmets

Technical Specifications



Designed to offer outstanding protection, the Skullgard Protective Hat is the standard for welders and elevated temperature working environments, such as steel mills.

Skullgard hat shown with Fas-Trac® III Suspension



Features

- Tested to radiant heat loads producing temperatures up to, but not exceeding, 350F
- Superior top impact protection
- Hand-crafted in the U.S.

Markets

- Welding operations
- Steel and smelting plants
- General industry and manufacturing
- Construction
- Oil, gas and petrochemical

Customization

- 27+, factory applied reflective or retro-reflective stripes
- Multiple printing services: one-color logo or digital photo on the front of the helmet
- For additional details, visit msasafety.com KEYWORD: logo

Care & Maintenance

- Clean helmet assembly regularly with MSA's Confidence Plus Cleaning Solution (P/Ns 10009971 or 10032737) or mild soap (no detergents) and warm water
- Do not throw, drop, use as support or abuse helmet to ensure proper working condition
- Store helmet in clean, dry environment <49°C (120°F).

Service Life Guidelines

- Inspect the helmet before and after each use and replace any part(s) as required
- Always replace the helmet after it has withstood an impact or penetration. MSA recommends:
 - replacing the suspension after no more than 12 months of use
 - replacing the shell after no more than five (5) years of use
- The life of a Skullgard Helmet tends to exceed our suggested service life due to the increased rigidity of the helmet's materials and areas of use. However, as with other personal protective equipment, a Skullgard Helmet's life should ultimately be determined by routine daily inspection before and after use.
- Please consult user instructions for additional details

Specifications

STANDARDS COMPLIANCE	ANSI/ISEA Z89.1-2014
CLASSIFICATION	Type I, Class G
CERTIFICATION	Third-party by SEI
APPLICATION(S)	General Purpose; Elevated Temperatures
PRODUCT SIZES	Small (6" to 7 1/8")— <i>natural tan cap style</i> Standard (6 1/2" to 8") Large (7" to 8 1/2")— <i>natural tan cap style only</i>
SHELL MATERIAL	Phenolic
AVAILABLE STYLES	Cap (Unslotted) Hat (Unslotted)
AVAILABLE SUSPENSIONS	Fas-Trac® III Ratchet Staz-On® Pinlock Closure 1-Touch Slide Closure Swing Ratchet
REQUIREMENTS FOR OPTIONAL FEATURES (Z89.1)	Reverse Donning, Lower Temperature, Higher Temperature, Hi-Viz (as indicated)
COLORS	9 (stocked for caps) 5 (stocked for hats) Other color options available, including custom colors
OTHER PPE	MSA accessories, including welding lugs, V-Gard Face Protection System, Winter Liners and chinstraps
PRODUCT DIMENSIONS	
CAP	11" x 8.5" x 5.25", 0.94 lb
HAT	12" x 10.5" x 6", 1.12 lb
MIN ORDER QUANTITIES (MOQ)	16 (stocked colors) 96 (non-stocked colors) 496 (custom colors)
SHIPPING CARTON DIMENSIONS (BOX OF 20)	
CAP	22.5" x 18.25" x 15", 20.2 lb
HAT	25.1875" x 21.75" x 15.5", 22.7 lb

Technical Assistance/Additional Information

For more information about Skullgard Helmets and other MSA products, please contact MSA Customer Service at 1-800-MSA-2222 or visit MSAsafety.com.

MSA – The Safety Company
1000 Cranberry Woods Drive
Cranberry Township, PA 16066 USA
Phone 724-776-8600
www.MSAsafety.com

U.S. Customer Service Center
Phone 1-800-MSA-2222
Fax 1-800-967-0398

MSA Canada
Phone 1-800-672-2222
Fax 1-800-967-0398