



3X32D

Technical Data

Color	Natural
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	16.54 x 11.02 x 17.32
Case Weight (lbs)	25.35
Country of Origin	Pakistan
Liner Material	Kevlar
Hide	Top Grain Goatskin
Cuff	Slip-on
Impact Protection	--
Construction	Cut-and-Sewn
Certifications	--
Product Circularity	--

PIP®

Top Grain Goatskin / Split Cowhide Leather Drivers Glove with Kevlar® Lining - Straight Thumb

- Top Grain Goatskin leather palm is soft, abrasion-resistant and is highly recommended for applications requiring tactile sensitivity
- Top Grain leather is smooth, provides durability and dexterity
- Split Cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Split leather is economical and has a visible texture
- Drivers gloves feature slip-on styling to provide good fit and comfort
- Kevlar® fiber liner provides high tensile strength relative to its weight, is inherently cut resistant and will not melt, ignite or conduct electricity

Applications

- Cut Resistance with Light Heat Protection
- Automotive Applications
- Glass Operations

Performance Data

ANSI Cut Level (2016)	A4
ANSI Abrasion Level	--
ANSI Puncture Level	--
ANSI Impact Level	--
ANSI Contact Heat Level	--
EN 388	3X32DX
ASTM F1358 Vertical Flame Level	--
EN 407	--

Care Instructions



Do Not Wash



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
09-K3720/S	Natural	S	616314159091	01616314159090	02616314159099
09-K3720/M	Natural	M	616314159084	01616314159083	02616314159082
09-K3720/L	Natural	L	616314159077	01616314159076	02616314159075
09-K3720/XL	Natural	XL	616314159107	01616314159106	02616314159105
09-K3720/XXL	Natural	2XL	616314159114	01616314159113	02616314159112