



## Technical Data

Color	Orange
Sizes Available	6-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 12.80
Case Weight (lbs)	10.32
Country of Origin	Malaysia
Material	Rubber
Length	11"
Cuff	Straight
Cuff Color	Orange
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

## NOVAX®

### Class 0 Rubber Insulating Glove with Straight Cuff - 11"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meets ANSI/ASTM D120 standard for use around electrical hazards
-  **WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

## Performance Data

Electrical Class	Class 0
------------------	---------

## Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
147-0-11/6	Orange	6	616314770227	10616314770224	20616314770221
147-0-11/7	Orange	7	616314050756	01616314050755	02616314050754
147-0-11/8	Orange	8	616314038068	01616314038068	02616314038068
147-0-11/8.5	Orange	8.5	616314339080	10616314339087	20616314339084
147-0-11/9	Orange	9	616314038075	01616314038075	02616314038075
147-0-11/9.5	Orange	9.5	616314260872	01616314260871	02616314260870
147-0-11/10	Orange	10	616314038082	01616314038082	02616314038082
147-0-11/10.5	Orange	10.5	616314260889	01616314260888	02616314260887
147-0-11/11	Orange	11	616314038099	01616314038099	02616314038099
147-0-11/12	Orange	12	616314057847	01616314058614	02616314058613