




Hi-Voltage AC™

Semi-Rimless Safety Glasses with Blue Frame, I/O Lens and Anti-Scratch Coating

- Unisex styling looks great on both men and women
- Designed to provide a great fit for smaller faces using a narrow nose bridge and frame
- Adjustable length temples with rubber tips provide a comfortable fit
- Oversized rubber nose pads offer a more secure fit
- 10 Base curve lens
- Meets ANSI Z87.1+
-  **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Artificial Light
- Indoor/Outdoor Work
- Fork Lift Operation



Technical Data

Color	Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 11.81 x 12.99
Case Weight (lbs)	14.33
Country of Origin	Taiwan
Lens	Indoor Outdoor
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Narrow Face
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Adjustable Length
Diopter	--
Base Curve	10
Construction	--
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Care Instructions

KEY:  Made from recycled or bio-based  Launderable  Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-22



SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
250-21-0400	Black	Clear	Clear	AS	616314031984	01616314031984	02616314031984
250-21-0401	Black	Tinted	Gray	AS	616314031991	01616314031991	02616314031991
250-21-0402	Black	I/O	Clear	AS	616314032004	01616314032004	02616314032004
250-21-0403	Black	Tinted	Light Blue	AS	616314161933	01616314161932	02616314161931
250-21-0409	Black	Tinted	Amber	AS	616314063565	01616314063564	02616314063563
250-21-0420	Black	Clear	Clear	AS/AF	616314032011	01616314032011	02616314032011
250-21-0421	Black	Tinted	Gray	AS/AF	616314067204	01616314067203	02616314067202
250-21-0100	Blue	Clear	Clear	AS	616314024887	01616314024887	02616314024887
250-21-0101	Blue	Tinted	Gray	AS	616314024894	01616314024894	02616314024894
250-21-0102	Blue	I/O	Clear	AS	616314025310	01616314025310	02616314025310
250-21-0120	Blue	Clear	Clear	AS/AF	616314025303	01616314025303	02616314025303

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated