



Nitrile

Black nitrile gloves that mask stains

- The distinctive color of these black nitrile gloves hides stains and provides contrast for improved visibility
- These disposable grip gloves feature a fully textured design for a confident grip
- Non-foaming for easy handling of objects in wet environments
- Tested against both fentanyl and gastric acid (vomit) to simulate hazardous, real world overdose situations



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Machinery and Equipment
- Healthcare
- Emergency Medical Services
- Utilities
- Warehousing

Recommended For

- Inspection, selecting, checking parts
- General Purpose Auto Aftermarket
- Use of cleaning tools and robotic equipment
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Maintaining lab furniture and equipment
- Sample taking and processing
- Blending, compounding solids and liquids
- Raw material sample collection
- Weighing and dispensing of solid and liquid raw materials
- Inspection (picking, checking and marking)
- Standard, moderate risk examination procedures
- Protection from Type I latex allergy in HCW's or patients



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	MidKnight® MK-296
Material	Nitrile
Color	Black
Glove Design	Chlorinated, Powder-Free, Silicone Free, Fully Textured
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 13485:2003
Regulatory	ASTM D6319, EN 1149-1/2/3, EN 420:2003 + A1:2009, FDA21 CFR 177-2600-US Food Contact Approved, Food Type: Rubber, ISO 11193, US QSR/FDA 510(k) Medical Examination Grade
Packaging	100 gloves per dispenser 10 dispensers per case 1000 gloves per case Also available in retail packs: 10 gloves per pack 50 packs per carton/case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Malaysia
User Needs Segment	Robust
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11)
Anti-static	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.12 / 4.7		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.15 / 5.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 27	≥ 24	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 10	≥ 11	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	MK-296-XS	MK-296-S	MK-296-M	MK-296-L	MK-296-XL	MK-296-XXL

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.