



Nitrile

Sturdy protection for demanding jobs

- Durable nitrile formulation for demanding jobs
- Sturdy design for longer wear times
- Exceptional barrier integrity with 0.65 AQL for allowable pinholes
- Textured fingertips provide secure grip



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Healthcare
- Agriculture
- Emergency Medical Services
- Utilities
- Warehousing

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Picking and fastening components
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Maintaining lab furniture and equipment
- Assembly of parts
- Sample taking and processing
- Raw material sample collection
- Higher-risk clinical applications
- Protection from Type I latex allergy in HCW's or patients



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	Supreno® SE SU-690
Material	Nitrile
Color	Violet Blue
Glove Design	Chlorinated, Powder-Free, Textured Fingers
Cuff	Beaded
Manufacturing/QMS Audit Standards	EN ISO 13485:2012
Regulatory	ASTM D6319, Food Type: Rubber, EN 1149-1/2/3, EN 420:2003 + A1:2009, FDA21 CFR 177-2600-US Food Contact Approved, US QSR/FDA 510(k) Medical Examination Grade
Packaging	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Malaysia
User Needs Segment	Robust
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Anti-static	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.18 / 7.1		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 32	≥ 30	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 10	≥ 11	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	SU-690-XS	SU-690-S	SU-690-M	SU-690-L	SU-690-XL

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.