



SAFETY DATA SHEET

1. Identification

Product identifier 2-26® Multi-Purpose Precision Lubricant - 1 gal

Other means of identification

Product Code No. 02006 (Item# 1003165)

Recommended use Multi-purpose lubricant

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

**24-Hour Emergency
(CHEMTREC)** 800-424-9300 (US)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards Not classified.

Health hazards Aspiration hazard Category 1

Environmental hazards Hazardous to the aquatic environment, acute hazard Category 2

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement May be fatal if swallowed and enters airways.

Precautionary statement

Prevention Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area.

Response If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting.

Storage Store locked up.

Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.

**Hazard(s) not otherwise
classified (HNOC)** None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrotreated light		64742-47-8	70 - 80

Chemical name	Common name and synonyms	CAS number	%
white mineral oil		8042-47-5	10 - 20
butyl stearate		123-95-5	3 - 5
petrolatum		8009-03-8	1 - 3
distillates (petroleum), hydrotreated heavy paraffinic		64742-54-7	0.1 - 1

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Move to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Rinse with water. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Powder. Dry chemicals. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	Cool containers exposed to heat with water spray and remove container, if no risk is involved. Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Will burn if involved in a fire. No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Use water spray to reduce vapors or divert vapor cloud drift. This product is miscible in water. This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways. Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.
Environmental precautions	Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.
--------------------------------------	---

8. Exposure controls/personal protection

Occupational exposure limits

U.S. - OSHA

Components

Type

Value

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

TWA

5 mg/m3

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components

Type

Value

Form

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

PEL

5 mg/m3

Mist.

petrolatum (CAS
8009-03-8)

PEL

5 mg/m3

Mist.

white mineral oil (CAS
8042-47-5)

PEL

5 mg/m3

Mist.

ACGIH

Components

Type

Value

Form

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

TWA

5 mg/m3

Inhalable fraction

US. ACGIH Threshold Limit Values

Components

Type

Value

Form

butyl stearate (CAS
123-95-5)

TWA

3 mg/m3

Respirable fraction.

10 mg/m3

Inhalable fraction.

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

TWA

5 mg/m3

Inhalable fraction.

petrolatum (CAS
8009-03-8)

TWA

5 mg/m3

Inhalable fraction.

white mineral oil (CAS
8042-47-5)

TWA

5 mg/m3

Inhalable fraction.

U.S. - NIOSH

Components

Type

Value

Form

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

STEL

10 mg/m3

Mist

TWA

5 mg/m3

Mist

US. NIOSH: Pocket Guide to Chemical Hazards

Components

Type

Value

Form

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

STEL

10 mg/m3

Mist.

TWA

5 mg/m3

Mist.

distillates (petroleum),
hydrotreated light (CAS
64742-47-8)

TWA

100 mg/m3

petrolatum (CAS
8009-03-8)

STEL

10 mg/m3

Mist.

TWA

5 mg/m3

Mist.

white mineral oil (CAS
8042-47-5)

STEL

10 mg/m3

Mist.

TWA

5 mg/m3

Mist.

Biological limit values	No biological exposure limits noted for the ingredient(s).
Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Nitrile. Neoprene.
Other	Wear suitable protective clothing.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance	
Physical state	Liquid.
Form	Liquid.
Color	Amber.
Odor	Mild petroleum.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-56.2 °F (-49 °C) estimated
Initial boiling point and boiling range	Not available.
Flash point	200.0 °F (93.3 °C) Setaflash
Evaporation rate	Slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	0.5 % estimated
Flammability limit - upper (%)	5.5 % estimated
Vapor pressure	0.1 hPa estimated
Vapor density	> 1 (air = 1)
Relative density	0.82
Solubility(ies)	
Solubility (water)	Negligible.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	428 °F (220 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Percent volatile	70 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.

Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides. Sulfur oxides. Hydrogen sulfide. Mercaptans. Sulfides.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	Based on available data, the classification criteria are not met.
Eye contact	Based on available data, the classification criteria are not met.
Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics	Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea.
---	---

Information on toxicological effects

Acute toxicity	May be fatal if swallowed and enters airways.
-----------------------	---

Components	Species	Test Results
distillates (petroleum), hydrotreated light (CAS 64742-47-8)		
Acute		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Inhalation		
LC50	Rat	> 20 mg/l, 4 Hours > 5 mg/l, 4 hours
Oral		
LD50	Rat	> 5000 mg/kg

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
----------------------------------	--

Serious eye damage/eye irritation	Direct contact with eyes may cause temporary irritation.
--	--

Respiratory or skin sensitization

Respiratory sensitization	Not a respiratory sensitizer.
Skin sensitization	This product is not expected to cause skin sensitization.

Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
-------------------------------	--

Carcinogenicity	Not classifiable as to carcinogenicity to humans.
------------------------	---

IARC Monographs. Overall Evaluation of Carcinogenicity

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	3 Not classifiable as to carcinogenicity to humans.
white mineral oil (CAS 8042-47-5)	3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
------------------------------	--

Specific target organ toxicity - single exposure	Not classified.
---	-----------------

Specific target organ toxicity - repeated exposure	Not classified.
---	-----------------

Aspiration hazard	May be fatal if swallowed and enters airways.
--------------------------	---

Chronic effects	Prolonged inhalation may be harmful.
------------------------	--------------------------------------

12. Ecological information

Ecotoxicity	Toxic to aquatic life.
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
Bioaccumulative potential	
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazardous waste code	Not regulated.
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.

15. Regulatory information

US federal regulations	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)	Not regulated.
SARA 304 Emergency release notification	Not regulated.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)	Not listed.
CERCLA Hazardous Substance List (40 CFR 302.4)	Not listed.
CERCLA Hazardous Substances: Reportable quantity	Not listed.
Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.	
Other federal regulations	
Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List	Not regulated.
Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)	Not regulated.
Safe Drinking Water Act (SDWA)	Not regulated.
Food and Drug Administration (FDA)	Not regulated.
Superfund Amendments and Reauthorization Act of 1986 (SARA)	
Classified hazard categories	Aspiration hazard
SARA 302 Extremely hazardous substance	Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)
Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Massachusetts RTK - Substance List

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
petrolatum (CAS 8009-03-8)
white mineral oil (CAS 8042-47-5)

US. Pennsylvania Worker and Community Right-to-Know Law

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
petrolatum (CAS 8009-03-8)
white mineral oil (CAS 8042-47-5)

US. Rhode Island RTK

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
petrolatum (CAS 8009-03-8)
white mineral oil (CAS 8042-47-5)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)
distillates (petroleum), hydrotreated light (CAS 64742-47-8)
petrolatum (CAS 8009-03-8)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 51.100(s)) 100 %

Consumer products (40 CFR 59, Subpt. C) Not regulated

State

Consumer products This product is regulated as a Multi-Purpose Lubricant. This product is compliant for use in all 50 states.

VOC content (CA) 0 %

VOC content (OTC) 0 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes

Country(s) or region	Inventory name	On inventory (yes/no)*
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes
*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s) A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).		

16. Other information, including date of preparation or last revision

Issue date	10-28-2020
Prepared by	Allison Yoon
Version #	01
Further information	CRC # 591C/1002617
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	This document has undergone significant changes and should be reviewed in its entirety.