





Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.



T1 T2 T3 T4 locations on back side
correspond to S1 S2 S3 S4 on front side

HEATING SURFACE null ft²
NETWEIGHT 103.9 lb
OPERATING WEIGHT Error lb
PLATE MATERIAL ALLOY 316
PLATE GROUPING 1*39H/1*40H

ALL DIMENSIONS IN INCHES

SIDE	MEDIA	INLET	TEMP.	OUTLET	TEMP.	FLOW RATE	PRESSURE DROP	LIQUID VOL.
1	Water	S1	33.8 °F	S2	32.0 °F	0 lb/h	null psi	0.35 ft ³
2	Water	S3	30.2 °F	S4	32.0 °F	0 lb/h	null psi	0.34 ft ³

PRESSURE VESSEL APPROVAL

UL/CRN

AlfaNova HP 76-80H (3287000921)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

COMPANY / REF.
Alfa Laval Nordic AB

TOTAL LENGTH 11.0 in
TOTAL WIDTH 7.5 in
TOTAL HEIGHT 24.3 in

7/7/2017
REV 0