

- Full-function remote control
- Programmable 24-hour timer cools on your schedule
- Removable and washable air filter
- Window venting kit with exhaust hose included
- Quick and easy operation
- Digital control panel
- Cool, Dehumidify and Fan Only modes
- Power Failure Auto Restart

Experience portable comfort wherever you are with the Amana 8,000 BTU portable air conditioner. Designed for cooling and dehumidifying a room up to 150 square feet, this Amana portable air conditioner features on-board electronic controls with 2 speeds and a 24-hour timer, plus a handy remote control. Easy-rolling caster wheels allow you to conveniently move the unit from room to room, providing cool air when and where you need it most. With the included window exhaust kit, it only takes a few minutes to uninstall and reinstall. At Amana we have exactly what you need to keep cool and comfortable.

MODEL	AMAP064AW
-------	-----------

PERFORMANCE

BTU Performance (Cooling)	7,000
Control Type	Electronic
Cooling Range	Up to 200 sq. ft.
EER	8.3
ENERGY STAR®	No
Dehumidification (Pts. / Hr.)	1.5
Air Flow (CFM): High / Low	123 / 98
Indoor Noise Level (dBA): High / Low	53 / 51
Refrigerant Type	R410A

ELECTRICAL RATINGS

Voltage / 60 Hz	115 V
Amps	6.5
Watts	840 W

FEATURES

Cooling Speeds	High, Low
Heat Option	No
Remote Controller	Yes
Power Failure Auto Restart	Yes
Energy Saver Mode	No
Programmable Timer	Yes
Fan Only Option	Yes
Sleep Mode	No
Reusable Filter	Yes
Filter Alert	No

DIMENSIONS / WEIGHT

Product Dimensions: W x D x H (in.)	15.2" x 14" x 25.2"
Product Weight (lbs.)	49.6
Shipping Dimensions: W x D x H (in.)	18.6" x 17.8" x 26"
Shipping Weight (lbs.)	58.4

