

Keystone dehumidifiers removes excess moisture from the air in any room in your home. Place this unit in various locations throughout your home or apartment such as the attic, bedroom, or basement. Features include electronic controls with LED display, a 24-hour timer, a transparent water level indicator and a full bucket alert with automatic shutoff. Continuous draining option is available using a low-level drain and a standard garden hose (garden hose not included). It also has a removable, easy-cleaning dust filter with a clean-filter alert. The auto-restart saves your settings during a power outage and the rolling casters make the unit easy to move to another location.



Dehumidifiers

MODEL	KSTAD224E	KSTAD354E	KSTAD504E	KSTAD506PE
PERFORMANCE				
Dehumidification	22 Pints	35 Pints	50 Pints	50 Pints
Coverage Area	1500-sq. ft.	3000-sq. ft.	4500-sq. ft.	1500-sq. ft.
Tank Capacity	0.8 Gal	0.8 Gal	1.8 Gal	1.8 Gal
ELECTRICAL				
Volts	115V	115V	115V	115V
Amps	3.1	4.7	6.5	6.5
Watts	250	520	720	720
Power Cord Length (Feet)	7	7	7	7
Plug Type	SP007	SP007	SP007	SP007
FEATURES				
Control Type	Electronic	Electronic	Electronic	Electronic
Display	LED	LED	LED	LED
Full Bucket Alert	Yes	Yes	Yes	Yes
24-Hour Timer	Yes	Yes	Yes	Yes
Auto Shut-off	Yes	Yes	Yes	Yes
Programmable Timer	Yes	Yes	Yes	Yes
Energy Star Rated	Yes	Yes	Yes	Yes
Air CFM (High/Low)	230/200	320/280	370/320	370/320
Filter Type	Washable	Washable	Washable	Washable
Warranty	1 year parts and labor	1 year parts and labor	1 year parts and labor	1 year parts and labor
SPECIFICATIONS				
Refrigerant	R410A	R410A	R410A	R410A
Product Dims (WxHxD) inches	15.2x19.69x10.24	15.43x24.25x11.1	15.43x24.25x11.1	15.43x24.25x11.1
Product Weight (lbs.)	33.07	40.56	42.11	42.11
Shipping Dims (WxHxD) inches	16.54x20.94x11.69	16.93x25.87x12.99	16.93x25.87x12.99	16.93x25.87x12.99
Shipping Weight (lbs.)	35.49	43.61	45.19	45.19