

At Keystone, your family's comfort starts here. Keystone offers a full assortment of budget-friendly Home Comfort Solutions for every room in the house. Whatever air conditioner type you need – window, window/wall, thru-the-wall, or portable – Keystone has you covered. We even have AC models with heating options! Keystone's assortment of flexible Window/Wall Air Conditioners is designed with a removable chassis so you can install them either in a window or through an exterior wall. Our two-in-one installation marvel includes an adjustable window kit for convenient window installation. For wall installation, you can use an existing compatible wall sleeve or purchase one of ours separately. Coveted features include a programmable timer, sleep mode, and energy saver mode.



Window Air Conditioners

MODEL	KSTAW15CE	KSTAW18C	KSTAW25C
PERFORMANCE			
BTU Capacity	15,100 BTU	18,000/17,700 BTU	25,000/24,700 BTU
Dehumidification (pints/hour)	3.2	3.8	2.2
Cooling Area	700-sq. ft.	1000-sq. ft.	350-sq. ft.
EER	11.8	11.8	2.8
ELECTRICAL			
Volts	115V	230V	230V
Amps	11.5	7.0/7.5	11.3/12.4
Watts	1279	1525/1500	2427/2398
Power Cord Length (Feet)	6.5	6.5	6.5
Plug Type (NEMA)	NEMA 5-15P	NEMA 5-15P	NEMA 5-15P
FEATURES			
Control Type	Electronic	Electronic	Electronic
Number of Fan Speeds	3	3	3
Energy Saving Mode	Yes	Yes	Yes
Sleep Mode	Yes	Yes	Yes
Check Filter Indicator	Yes	Yes	Yes
Programmable Timer	Yes	Yes	Yes
Energy Star Rated	No	No	No
Remote Control	Yes	Yes	Yes
Air CFM (Fan Speeds)	250/308/353	280/320/360	445/485/523
Air Direction Control	4-way	4-way	4-way
Filter Type	Washable	Washable	Washable
Warranty	1 Yr parts & labor/5 Yr sealed system	1 Yr parts & labor/5 Yr sealed system	1 Yr parts & labor/5 Yr sealed system
SPECIFICATIONS			
Refrigerant	R32	R410A	R410A
Product Dims (WxHxD) inches	23.6x17.9x25.4	23.6x17.9x25.4	26.5x18.6x26.5
Product Weight (lbs.)	102.30	102.3	130.1
Shipping Dims (WxHxD) inches	30x20.2x26	30x20.2x26	31.3x21.1x29.5
Shipping Weight (lbs.)	118	118	145.7