

Through the Wall

Air Conditioners

Cool Only



Whirlpool takes comfort and caring to the next level. Our line of home comfort products keeps the climate inside your home just right - making the air comfortable, clean, and fresh. Whirlpool's through-the-wall air conditioners are compatible with standard wall sleeves and offer a permanent cooling solution for areas of your home that are not connected to a central cooling system, saving you the hassle of summer installation then winter storage season after season. Trust Whirlpool to help you care for your family and make your life easier.



Cool Only Through-the-Wall
Air Conditioners

MODEL	WHAT081-1AW	WHAT101-1AW	WHAT102-2BW	WHAT121-1AW	WHAT122-2AW	WHAT142-2AW
PERFORMANCE						
BTUs	8,000	10,000	10,000	12,000	12,000	14,000
Cooling Range (Sq. Ft.)	300-350	400-450	400-450	450-550	450-550	550-700
Control Type	Electronic	Electronic	Electronic	Electronic	Electronic	Electronic
EER	10.7	10.7	10.7	10.6	10.6	9.4
ENERGY STAR	Yes	Yes	Yes	Yes	Yes	No
Dehumidification	0.8	1.2	1.2	1.7	1.7	2.1
Air Flow (CFM) (High/Med/Low)	247/229/212	265/247/229	265/247/229	276/259/241	276/259/241	265/247/229
Refrigerant Type	R410A	R410A	R410A	R410A	R410A	R410A
ELECTRICAL RATINGS						
Voltage (V) / Frequency (Hz)	115v / 60Hz	115v / 60Hz	230/208v / 60Hz	115v / 60Hz	230v/208v / 60Hz	230v/208v / 60Hz
Cooling Amps	6.9	8.3	4.2/4.5	10.1	5.1/5.4	6.7/7.2
Cooling Watts	755	940	940/920	1130	1130/1090	1490/1450
FEATURES						
Air Direction	8-way	8-way	8-way	8-way	8-way	8-way
Cooling Speeds	High, Medium, Low	High, Medium, Low	High, Medium, Low	High, Medium, Low	High, Medium, Low	High, Medium, Low
Remote Control	Yes	Yes	Yes	Yes	Yes	Yes
Power Failure Auto Restart	Yes	Yes	Yes	Yes	Yes	Yes
Power Saver Mode	Yes	Yes	Yes	Yes	Yes	Yes
Programmable Timer	Yes	Yes	Yes	Yes	Yes	Yes
Fan Only Option	Yes	Yes	Yes	Yes	Yes	Yes
Sleep Mode	Yes	Yes	Yes	Yes	Yes	Yes
Reusable Filter	Yes	Yes	Yes	Yes	Yes	Yes
Filter Alert	Yes	Yes	Yes	Yes	Yes	Yes
DIMENSIONS / WEIGHT						
Product Dimensions (in.) LxWxH	20.3x24.2x14.5	20.3x24.2x14.5	20.3x24.2x14.5	20.3x24.2x14.5	20.3x24.2x14.5	20.3x24.2x14.5
Product Weight (lb.)	63.93	73.85	73.85	74.96	74.96	76.06
Warranty	1 Year Replacement	1 Year Replacement	1 Year Replacement	1 Year Replacement	1 Year Replacement	1 Year Replacement
UPC Code	192487079461	192487079478	192487079485	192487079492	192487079508	192487079515

Through the Wall

Air Conditioners

Heat & Cool



Trust Whirlpool to help you care for your family and make your life easier. Our line of home comfort products keeps the climate inside your home just right - making the air comfortable, clean, and fresh. Whirlpool's through-the-wall air conditioners are compatible with standard wall sleeves and offer a permanent cooling solution for areas of your home that are not connected to a central cooling system, saving you the hassle of summer installation then winter storage season after season. In addition, our heat/cool units provide **supplemental heating** to warm up the room on those unexpected chilly nights without heating the entire house. Take comfort and caring to the next level with Whirlpool.



Heat & Cool Through-the-Wall Air Conditioners

MODEL	WHAT081-HAW	WHAT101-HAW	WHAT121-HAW	WHAT141-HAW
PERFORMANCE				
BTUs (Cool/Heat)	8,000/4,200	10,000/10,600	12,000/10,600	14,000/10,600
Cooling Range (Sq. Ft.)	300-350	400-450	450-550	550-700
Control Type	Electronic	Electronic	Electronic	Electronic
EER	9.7	9.7	9.7	9.4
ENERGY STAR	No	No	No	No
Dehumidification	0.7	1.2	1.6	2.1
Air Flow (CFM)	247/229/212	265/247/229	276/259/241	265/247/229
Refrigerant Type	R410A	R410A	R410A	R410A
ELECTRICAL RATINGS				
Voltage (V) / Frequency (Hz)	115v / 60Hz	230v/208v / 60Hz	230v/208v / 60Hz	230v/208v / 60Hz
Cooling Amps	7.2	4.6/4.9	5.5/5.9	6.7/7.2
Cooling Watts	810	1030/1000	1230/1190	1490/1450
Heating Amps	12.5	15/13.5	15/13.6	15/13.7
Heating Watts	1450	3450/2850	3450/2851	3450/2852
FEATURES				
Air Direction	8-way	8-way	8-way	8-way
Cooling Speeds	High, Medium, Low	High, Medium, Low	High, Medium, Low	High, Medium, Low
Heating Speeds	High, Medium, Low	High, Medium, Low	High, Medium, Low	High, Medium, Low
Remote Control	Yes	Yes	Yes	Yes
Power Failure Auto Restart	Yes	Yes	Yes	Yes
Power Saver Mode	Yes	Yes	Yes	Yes
Programmable Timer	Yes	Yes	Yes	Yes
Fan Only Option	Yes	Yes	Yes	Yes
Sleep Mode	Yes	Yes	Yes	Yes
Reusable Filter	Yes	Yes	Yes	Yes
Filter Alert	Yes	Yes	Yes	Yes
DIMENSIONS / WEIGHT				
Product Dimensions (in.) LxWxH	20.3x24.2x14.5	20.3x24.2x14.5	20.3x24.2x14.5	20.3x24.2x14.5
Product Weight (lb.)	66.14	75	76.06	77.16
Warranty	1 Year Limited	1 Year Limited	1 Year Limited	1 Year Limited
UPC Code	192487130865	192487130858	192487130872	192487130889