

SECTION 1 PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME:	Fasson 0808	MANUFACTURER:	Avery Dennison Performance Tapes NA 250 Chester Street Painesville, OH 44077 Telephone: 440-358-2600
PART NUMBER:	57432		
PRODUCT FAMILY:	Pressure sensitive tape	DATE PREPARED:	5/31/15

SECTION 2 HAZARDS IDENTIFICATION

This product is classified as an Article and is not hazardous nor does it contain hazardous ingredients over trace amounts as defined under 29 CFR 1910.1200

SECTION 3 COMPOSITION/INFORMATION ON INGREDIENTS

Hazardous Components: None

SECTION 4 FIRST AID MEASURES

INHALATION: None

EYE CONTACT: For eyes, mechanical injury only. Check for evidence of corneal injury

SKIN CONTACT:

INGESTION: Unlikely due to physical form. No first aid measures needed

SECTION 5 FIRE FIGHTING MEASURES

FLAMMABLE PROPERTIES

FLASH POINT:	N/A	FLAMMABLE	LEL	UEL
METHOD USED:	N/A	LIMITS	N/A	N/A

EXTINGUISHING MEDIA: Water or dry chemical

SPECIAL FIRE FIGHTING PROCEDURES: Treat as ordinary combustible

UNUSUAL FIRE AND EXPLOSION HAZARDS: Ordinary products of combustion

SECTION 6 ACCIDENTAL RELEASE MEASURES

STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED: N/A

PRODUCT NAME: Fasson 0808	PART NUMBER: 57432
----------------------------------	---------------------------

SECTION 7 HANDLING AND STORAGE

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORING:
Keep away from high heat and flames

SECTION 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

RESPIRATORY PROTECTION: None required

VENTILATION: (X) LOCAL EXHAUST () MECHANICAL
Normal ventilation adequate for most operations

PROTECTIVE GLOVES: Not needed

EYE PROTECTION: Not needed

OTHER PROTECTIVE EQUIPMENT: N/A

WORK/HYGIENIC PRACTICES: No unusual practices needed

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

BOILING POINT:	N/A	WEIGHT PER GALLON:	N/A
VAPOR PRESSURE (MM HG.):	N/A	% VOLATILE BY WEIGHT:	<1.0 wt%
VAPOR DENSITY (AIR = 1):	N/A	EVAPORATION RATE:	N/A
% SOLUBILITY IN WATER:	<1%	PH:	N/A
PHYSICAL FORM:	Solid	ODOR:	Slight odor

SECTION 10 STABILITY AND REACTIVITY

STABILITY: (X) STABLE () UNSTABLE

CONDITIONS TO AVOID: None known

INCOMPATIBILITY (MATERIALS TO AVOID): None known

HAZARDOUS DECOMPOSITION OR BYPRODUCTS: None known

HAZARDOUS POLYMERIZATION: () MAY OCCUR (X) WILL NOT OCCUR

PRODUCT NAME: Fasson 0808	PART NUMBER: 57432
----------------------------------	---------------------------

SECTION 11 TOXICOLOGICAL INFORMATION

ROUTE(S) OF ENTRY: INHALATION: N/A
SKIN: N/A
INGESTION: Unlikely due to physical form

HEALTH HAZARDS: None

CARCINOGENICITY: Not carcinogenic

SIGNS AND SYMPTOMS OF EXPOSURE: N/A

SECTION 12 ECOLOGICAL INFORMATION

Material is non-toxic

SECTION 13 DISPOSAL CONSIDERATIONS

WASTE DISPOSAL METHOD:
Incinerate or landfill in accordance with Federal, State, and Local regulations

SECTION 14 TRANSPORT INFORMATION

Material is not DOT regulated

SECTION 15 REGULATORY INFORMATION

Material is considered an article and is not regulated

SECTION 16 OTHER INFORMATION

None

THIS SDS UTILIZES THE FORMAT RECOMMENDED BY ANSI Z400.1/Z129.1-2010. THE INFORMATION AND RECOMMENDATIONS CONTAINED HEREIN ARE BASED UPON DATA BELIEVED TO BE CORRECT. HOWEVER, NO GUARANTEE OR WARRANTY OF ANY KIND EXPRESSED OR IMPLIED IS MADE WITH RESPECT TO THE INFORMATION CONTAINED .

SDS PREPARED BY TECHNICAL DEPARTMENT