



ISO-9001 Registered Quality System.

**Sales, Service & Distribution Center**  
 Newark, NJ 07105  
 Phone: 973-589-9150 Fax: 973-589-4432

**Manufacturing, Sales, Service & Distribution Center**  
 Toledo, OH 43605  
 Phone: 419-691-2491 Fax: 419-693-3806

**Sales and Tech Service Support**  
 Phone: 1-800-733-4755

**PRODUCT DATA**

**LUBRIPLATE SPECIAL AUTO-MARINE GREASE**

**DESCRIPTION**

LUBRIPLATE Special Auto-Marine Grease is an NLGI 2 polymer type lubricant specifically designed for automotive and marine applications of all types. This lithium 12-hydroxy stearate grease is extremely shear stable and resistant to both fresh and salt water, making it the ideal lubricant for all marine and automotive needs.

**APPLICATIONS**

Marine uses include all pressure fitting applications including boat trailer wheel bearings, winch gears, deck machinery, ground tackle and turn-buckles.

Automotive applications include chassis, king pins, steering knuckles, bucket pins, ball joints and universal joints.

**ADVANTAGES**

- ⇒ Excellent extreme pressure/anti-wear properties
- ⇒ Extremely shear stable
- ⇒ High temperature characteristics
- ⇒ Very good sealing properties to keep out water and dirt
- ⇒ Outstanding resistance to fresh and salt water
- ⇒ Tenacious and adhesive to increase stay-put properties

**Typical Test Data**

PROPERTY	TEST METHOD	TYPICAL RESULTS*
Type of Base		Lithium 12-Hydroxy Stearate
Worked Penetration	ASTM D-217	265 - 295
NLGI No.		2
ASTM Dropping Point	ASTM D-566	400°F+/205°C+
Mineral Oil Viscosity: SUS @ 100°F	ASTM D-2161	1250
cSt @ 40°C	ASTM D-445	237
SUS @ 210°F	ASTM D-2161	95
cSt @ 100°C	ASTM D-445	19
Timken E.P. Test: OK Load	ASTM D-2783	60 lbs.
Four Ball E.P. Test: OK Load	ASTM D-2783	370 kg.
Load Wear Index	ASTM D-2266	64.3
Corrosion Prevention	ASTM D-1743	1,1,1
Copper Corrosion	ASTM D-130	1a
Oxidation Stability	ASTM D-942	3 psi/100 hours
Water Washout	ASTM D-1264	1.5%
Appearance	Visual	Tacky, Beige

**PACKAGING AVAILABLE**

**Part No.**

Carton, 12/16 oz. Plastic Tubs  
 Carton, 40/14½ oz. Cartridges

L0206-004  
 L0206-098

