



KYORENE®
THE GRAPHENE FIBER

00-002

SPECIFICATION SHEET



CUT



ABR



PUN

EN388



4121A



UPF
100

Oeko-Tex®
Standard 100

ATTRIBUTES:

- 15g Gray Kyorene® Graphene A1 Liner
- Black HCT® MicroFoam Nitrile Knuckle Coating

FEATURES:

- Knuckle Coating for Added Back of Hand Liquid Resistance
- Bacteriostatic Kills Harmful Bacteria
- Thermal Regulating to Keep the Hands Comfortable
- Odor Neutralizing to Keep the Gloves Smelling Fresh

APPLICATIONS:

- Automotive Manufacturing
- Light Manufacturing
- Maintenance
- Warehousing
- Landscaping

CATEGORY:

- Kyorene®

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:



KYORENE®
THE GRAPHENE FIBER



Hybrid Coating Technology

SPECIFICATIONS:

- **Liner Materials:** 15g Gray Kyorene® Graphene A1 Liner
- **Coating Materials:** Black HCT® MicroFoam Nitrile
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XS-XXL

Armor Guys Reference Number: 00-002

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	XXL
CUFF COLOR	Purple	Red	Yellow	Brown	Black	Blue
PER CASE	6DZ	6DZ	6DZ	6DZ	6DZ	6DZ

PERFORMANCE LEVEL:

EN388: 4121A – EN Level 1 Cut Resistance

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5
CUT TDM TEST	A	B	C	D	E	F



VERIFIED GRAPHENE®
PRODUCER
THE GRAPHENE COUNCIL

ARMOR GUYS
• PROTECTED •