



ATTRIBUTES:

- 13g Salt & Pepper HDPE A3 Basetek® Liner
- Gray Polyurethane Palm Coating

FEATURES:

- Positive Grip in Dry & Light Oil Environments

APPLICATIONS:

- Automotive Manufacturing
- Light Manufacturing
- Sheet Metal Handling
- Metal Stamping
- Construction

CATEGORY:

- Basetek®

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:



Innovative Fiber Technology

SPECIFICATIONS:

- **Liner Materials:** 13g Salt & Pepper HDPE A3 Basetek® Liner
- **Coating Materials:** Gray Polyurethane
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XXS-XXXL

Armor Guys Reference Number: 02-013

PACKAGING:

GLOVE SIZE	XXS	XS	S	M	L	XL	XXL	XXXL
CUFF COLOR	Pink	Purple	Red	Yellow	Brown	Black	Blue	Gray
PER CASE	12DZ							
CASE WEIGHT	17.62/lbs	18.28/lbs	18.94/lbs	20.81/lbs	21.74/lbs	23.79/lbs	26.65/lbs	29.30/lbs

PERFORMANCE LEVEL:

EN388: 4442C – EN Level 4 Cut Resistance

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5
CUT TDM TEST	A	B	C	D	E	F

⚠ This product can expose you to N,N-Dimethylformamide- which is known to the State of California to cause cancer. For more information go to www.P65warnings.ca.gov

ARMOR GUYS

• PROTECTED •