



PUN
EN388



ATTRIBUTES:

- 13g Blue HDPE A6 Basetek® Liner
- Black Polyurethane Palm Coating

FEATURES:

- Positive Grip in Dry & Light Oil Environments

APPLICATIONS:

- Automotive Manufacturing
- Metal Stamping
- Steel Handling
- Construction
- Recycling

CATEGORY:

- Basetek®

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:



Innovative Fiber Technology

SPECIFICATIONS:

- **Liner Materials:** 13g Blue HDPE A6 Basetek® Liner
- **Coating Materials:** Black Polyurethane
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XXS-XXL

Armor Guys Reference Number: 02-015

PACKAGING:

GLOVE SIZE	XXS	XS	S	M	L	XL	XXL
CUFF COLOR	Pink	Purple	Red	Yellow	Brown	Black	Blue
PER CASE	12DZ						
CASE WEIGHT	23.03/lbs	24.03/lbs	24.69/lbs	26.23/lbs	27.77/lbs	30.97/lbs	33.28/lbs

PERFORMANCE LEVEL:

EN388: 4X44E

ABRASION	0	1	2	3	4	5	X
CUT	0	1	2	3	4	5	X
TEAR	0	1	2	3	4	5	X
PUNCTURE	0	1	2	3	4	5	X
CUT TDM TEST	A	B	C	D	E	F	X

⚠ This product can expose you to N,N-Dimethylformamide- which is known to the State of California to cause cancer. For more information go to www.P65warnings.ca.gov