



SPECIFICATIONS:

- **Liner Materials:** 13" 15MIL Flock Lined
- **Coating Materials:** Green Nitrile
- **Origin:** PRC
- **Sizes:** XS-XXL

Armor Guys Reference Number: 05-003

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	XXL
PER CASE	12DZ	12DZ	12DZ	12DZ	12DZ	12DZ
CASE WEIGHT	17.40/lbs	18.06/lbs	18.72/lbs	19.82/lbs	20.93/lbs	21.59/lbs

PERFORMANCE LEVEL:

EN388: 3101X – EN Level 1 Cut Resistance

ABRASION	0	1	2	3	4	5	X
CUT	0	1	2	3	4	5	X
TEAR	0	1	2	3	4	5	X
PUNCTURE	0	1	2	3	4	5	X
CUT TDM TEST	A	B	C	D	E	F	X

ATTRIBUTES:

- 13" 15MIL Flock Lined
- Green Nitrile Coating

FEATURES:

- Diamond Pattern for Enhanced Grip
- Complies With FDA Food Handling Requirements (21 CFR 177.2600)

APPLICATIONS:

- Chemical Processing
- Food Processing
- Machining
- Printing Press Operations
- Oil & Gas
- Petrochemicals

CATEGORY:

- Chemiflex®

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:



Chemical Resistance

ARMOR GUYS
• PROTECTED •