

Main Tenant Circuit Breakers

Product Description

1MP, 1MM and 3MM Main Tenant Circuit Breakers

The following Cutler-Hammer breakers are to be used on 1MP, 1MM and 3MM modular metering stacks. They are 120/240 Vac — field installed.



BR2100



CC2200

Product Selection

Table 24. 1MP, 1MM and 3MM Main Tenant Circuit Breakers

Description	Number of Poles	Main Tenant Circuit Breaker Ampere Rating	Catalog Number				
			10,000 AIC	22,000 AIC	25,000 AIC	42,000 AIC	100,000 AIC
Plug-on type circuit breakers used with 1MP, 1MM and 3MM 125 ampere modular metering stacks	2	60	BR260	BRH260	—	BRHH260	—
	2	70	BR270	BRH270	—	BRHH270	—
	2	80	BR280	BRH280	—	BRHH280	—
	2	90	BR290	BRH290	—	BRHH290	—
	2	100	BR2100	BRH2100	—	BRHH2100	—
	2	110	BR2110	BRH2110	—	BRHH2110	—
Bolt-on type circuit breakers used with 1MP, 1MM and 3MM 200 ampere modular metering stacks	2	125	BR2125	BRH2125	—	BRHH2125	—
	2	60	—	—	CHH2060H2X	CHH2060H4X	CHH2060X
	2	70	—	—	CHH2070H2X	CHH2070H4X	CHH2070X
	2	80	—	—	CHH2080H2X	CHH2080H4X	CHH2080X
	2	90	—	—	CHH2090H2X	CHH2090H4X	CHH2090X
	2	100	CC2100X	—	CHH2100H2X	CHH2100H4X	CHH2100X
	2	125	CC2125X	—	CHH2125H2X	CHH2125H4X	CHH2125X
	2	150	CC2150X	—	CHH2150H2X	CHH2150H4X	CHH2150X
	2	175	CC2175X	—	CHH2175H2X	CHH2175H4X	CHH2175X
	2	200	CC2200X	—	CHH2200H2X	CHH2200H4X	CHH2200X