

Weatherproof outlet boxes

Single-gang

Applications:

- For use as a weatherproof junction box or device housing in damp or wet locations when combined with weatherproof cover

Features:

- Durable die cast aluminum construction for long product life
- Powder paint finish for corrosive environments
- Pre-installed ground screw
- Tapered NPT hubs
- Includes mounting hardware, lugs and closure plugs

Certifications and compliances:

- UL File No. E-121488
- CSA C22.2 No. 18
- Complies with NEC Article 406.9(B)(1)
- NEMA 3R



Standard material:

- Die cast aluminum



TP7010 - TP7018



TP7026, TP7034



TP7042, TP7050



TP7058, TP7066

SINGLE-GANG - 2" DEEP WITH LUGS

Cat. #	Outlet holes	Cubic inches	Color	Unit qty.	Wt. lbs. per 100
TP7010	3 - 1/2"	18.3	Gray	50	53.5
TP7010BULK	3 - 1/2"	18.3	Gray	50	53.5
TP7011	3 - 1/2"	18.3	White	50	53.5
TP7012	3 - 1/2"	18.3	Bronze	50	53.5
TP7018	3 - 3/4"	18.3	Gray	50	53.6
TP7019	3 - 3/4"	18.3	White	50	53.6
TP7020	3 - 3/4"	18.3	Bronze	50	53.6
TP7026	4 - 1/2"	17.0	Gray	50	55.9
TP7027	4 - 1/2"	17.0	White	50	55.9
TP7028	4 - 1/2"	17.0	Bronze	50	55.9
TP7034	4 - 3/4"	18.3	Gray	50	53.9
TP7035	4 - 3/4"	18.3	White	50	53.9
TP7036	4 - 3/4"	18.3	Bronze	50	53.9
TP7042	5 - 1/2"	18.3	Gray	50	56.0
TP7050	5 - 3/4"	17.0	Gray	50	55.5
TP7058	5 - 1/2" (side entry)	18.3	Gray	50	57.3
TP7066	5 - 3/4" (side entry)	18.0	Gray	50	53.9



TP7074, TP7078, TP7082

SINGLE-GANG - 2-5/8" DEEP WITH LUGS

Cat. #	Outlet holes	Cubic inches	Color	Unit qty.	Wt. lbs. per 100
TP7074	3 - 1/2"	25.5	Gray	25	64.3
TP7075	3 - 1/2"	25.5	White	25	64.3
TP7076	3 - 1/2"	25.5	Bronze	25	64.3
TP7078	3 - 3/4"	25.5	Gray	25	64.6
TP7082	3 - 1"	23.0	Gray	25	72.8

Weatherproof