

Compact circuit breakers, switch disconnectors

2.1

Circuit breakers UL/CSA, IEC, thermomagnetic releases, 3 pole
NZM...AF...NA

Fixed mounting with box terminals

Part no.

Article no.

Std. pack

Information relevant for export to North America



Part no.	Article no.	Std. pack	Information relevant for export to North America
NZMH2-AF15-BT-NA	107809	1 Off	Product Standards
NZMH2-AF20-BT-NA	107810		UL 489; CSA-C22.2 No. 5-09; IEC 60947-2; CE marking
NZMH2-AF25-BT-NA	107811		UL File No.
NZMH2-AF30-BT-NA	107812		E31593
NZMH2-AF35-BT-NA	107813		UL Category Control No.
NZMH2-AF40-BT-NA	107814		DIVQ
NZMH2-AF45-BT-NA	107815		CSA File No.
NZMH2-AF50-BT-NA	107816		022086
NZMH2-AF60-BT-NA	107817		CSA Class No.
NZMH2-AF70-BT-NA	107818		1432-01
NZMH2-AF80-BT-NA	107819		North America Certification
NZMH2-AF90-BT-NA	107820		UL listed, CSA certified
NZMH2-AF100-BT-NA	107821		Specially designed for NA
NZMH2-AF110-BT-NA	107822		Yes
NZMH2-AF125-BT-NA	107823		Suitable for
NZMH2-AF150-BT-NA	107824		Feeder circuits, branch circuits
NZMH2-AF175-BT-NA	107825		Current Limiting Circuit breaker
NZMH2-AF200-BT-NA	107826		Yes
NZMH2-AF225-BT-NA	107827		Max. Voltage Rating
NZMH2-AF250-BT-NA	107828		600Y/347 V, 480 V
			Degree of Protection
			IEC: IP20; UL/CSA Type: -