

H TIMING PULLEY BAR STOCK

0.500" Pitch

Steel



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
30H-PS10S	30	121.3 mm	119.9 mm	4.775"	4.721"	1.000"	1.000"	10.000"	11.000"
31H-PS10S	31	125.4 mm	124.0 mm	4.936"	4.882"	1.000"	1.000"	10.000"	11.000"
32H-PS10S	32	129.4 mm	128.0 mm	5.093"	5.039"	1.000"	1.000"	10.000"	11.000"
33H-PS10S	33	133.5 mm	132.1 mm	5.254"	5.200"	1.000"	1.000"	10.000"	11.000"
34H-PS10S	34	137.5 mm	136.1 mm	5.414"	5.360"	1.000"	1.000"	10.000"	11.000"
35H-PS10S	35	141.5 mm	140.2 mm	5.571"	5.519"	1.000"	1.000"	10.000"	11.000"
36H-PS10S	36	145.5 mm	144.2 mm	5.730"	5.676"	1.000"	1.000"	10.000"	11.000"
37H-PS10S	37	149.6 mm	148.3 mm	5.891"	5.837"	1.000"	1.000"	10.000"	11.000"
38H-PS10S	38	153.7 mm	152.3 mm	6.050"	5.996"	1.000"	1.000"	10.000"	11.000"
39H-PS10S	39	157.7 mm	156.4 mm	6.210"	6.156"	1.000"	1.000"	10.000"	11.000"
40H-PS10S	40	161.7 mm	160.3 mm	6.366"	6.312"	1.000"	1.000"	10.000"	11.000"



SAI GLOBAL

ISO 9001
Quality

B&B Manufacturing, Inc. is pleased to announce the certification of our Quality Management System to the ISO 9001:2008 standard. The certification of compliance with the ISO 9001:2008 standard recognizes that the policies, practices and procedures of B&B Manufacturing provide consistent quality in the products that we provide to our customers. B&B Manufacturing engaged in a demanding and detailed evaluation process of our entire quality management system with SAI Global. This evaluation reviewed system development, documentation, internal audits, clearance of non-conformances and every quality management procedure in the company. This proactive decision to become ISO 9001:2008 certified demonstrates our commitment to providing our customers with high quality precision mechanical components and power transmission products. It is another step in its commitment to continual improvement and customer service.