

# L TIMING PULLEY BAR STOCK

0.375" / 9.525 mm Pitch  
Steel



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
27L-PS8S	27	81.9 mm	81.1 mm	3.224"	3.194"	1.000"	1.000"	8.000"	9.000"
28L-PS8S	28	84.9 mm	84.1 mm	3.342"	3.312"	1.000"	1.000"	8.000"	9.000"
29L-PS8S	29	87.9 mm	87.2 mm	3.462"	3.432"	1.000"	1.000"	8.000"	9.000"
30L-PS8S	30	91.0 mm	90.2 mm	3.581"	3.551"	1.000"	1.000"	8.000"	9.000"
31L-PS8S	31	94.0 mm	93.3 mm	3.702"	3.672"	1.000"	1.000"	8.000"	9.000"
32L-PS8S	32	97.0 mm	96.3 mm	3.820"	3.790"	1.000"	1.000"	8.000"	9.000"
33L-PS8S	33	100.1 mm	99.3 mm	3.941"	3.911"	1.000"	1.000"	8.000"	9.000"
34L-PS8S	34	103.1 mm	102.3 mm	4.058"	4.028"	1.000"	1.000"	8.000"	9.000"
35L-PS8S	35	106.1 mm	105.4 mm	4.179"	4.149"	1.000"	1.000"	8.000"	9.000"
36L-PS8S	36	109.1 mm	108.4 mm	4.297"	4.267"	1.000"	1.000"	8.000"	9.000"

B&B Manufacturing is a leading American manufacturer and worldwide distributor of precision mechanical components. These components include but are not limited to:

gears  
gear racks  
roller chain sprockets

pulley bar stock  
pulley flanges  
timing pulleys

timing belts  
poly v sheaves  
poly v belts

idler pulleys  
idler sprockets  
tensioners

custom pulleys  
custom sprockets  
custom belts

