

MXL TIMING BELTS

0.080" Pitch

Standard Widths:

1/8", 3/16", 1/4", 3/8"

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts



Part Number	No. of Teeth	Pitch Length (in)
343MXL	343	27.440
347MXL	347	27.760
350MXL	350	28.000
354MXL	354	28.320
355MXL	355	28.400
356MXL	356	28.480
358MXL	358	28.640
359MXL	359	28.720
360MXL	360	28.800
364MXL	364	29.120
365MXL	365	29.200
371MXL	371	29.680
372MXL	372	29.760
380MXL	380	30.400
388MXL	388	31.040
390MXL	390	31.200
397MXL	397	31.760
400MXL	400	32.000
402MXL	402	32.160
405MXL	405	32.400
408MXL	408	32.640
410MXL	410	32.800
412MXL	412	32.960
413MXL	413	33.040
419MXL	419	33.520

Part Number	No. of Teeth	Pitch Length (in)
420MXL	420	33.600
421MXL	421	33.680
424MXL	424	33.920
425MXL	425	34.000
427MXL	427	34.160
431MXL	431	34.480
434MXL	434	34.720
435MXL	435	34.800
436MXL	436	34.880
440MXL	440	35.200
442MXL	442	35.360
447MXL	447	35.760
448MXL	448	35.840
453MXL	453	36.240
458MXL	458	36.640
463MXL	463	37.040
464MXL	464	37.120
466MXL	466	37.280
472MXL	472	37.760
473MXL	473	37.840
475MXL	475	38.000
480MXL	480	38.400
482MXL	482	38.560
487MXL	487	38.960
488MXL	488	39.040

Part Number	No. of Teeth	Pitch Length (in)
490MXL	490	39.200
493MXL	493	39.440
498MXL	498	39.840
500MXL	500	40.000
505MXL	505	40.400
516MXL	516	41.280
522MXL	522	41.760
524MXL	524	41.920
525MXL	525	42.000
532MXL	532	42.560
535MXL	535	42.800
540MXL	540	43.200
543MXL	543	43.440
546MXL	546	43.680
548MXL	548	43.840
550MXL	550	44.000
571MXL	571	45.680
579MXL	579	46.320
591MXL	591	47.280
592MXL	592	47.360
599MXL	599	47.920
600MXL	600	48.000
612MXL	612	48.960
648MXL	648	51.840
665MXL	665	53.200
694MXL	694	55.520

Neoprene MXL timing belt part numbers can be determined as follows:
 Tooth Count + MXL + Width Code + (G for fiberGlass reinforcement)
 Example: 1000MXL037G