



BAKERLUX™ LED Heavy-Duty Digital Countertop Convection Oven

Half Size 3 Shelves

BAKERLUX™ - baking ahead of its time



208-240
Volt

LED digital programmable controls:

- 3 BAKING STEPS
- 0 - inf TIMER
- 120° - 500° F TEMPERATURE
- 0-20-40-60-80-100% HUMIDITY
- 2 FAN SPEEDS
- PROOFER CONTROL
- 99 PROGRAMS
12 QUICK ACCESS



NEMA
6-20P
Plug

XAFT-03HS-LD: BAKERLUX™ LED Panel Heavy-Duty Countertop Convection Oven with Digital Controls & Humidity

Made to Cadco Ltd. specifications by UNOX S.p.A., Italy • NSF, MET to UL & CSA Standards
Cadco Model XAFT-03HS-LD = UNOX Model XAFT-03HS-ELDVS-US

FEATURES

- Advanced airflow design & automatically reversible fan for even baking
 - 3 baking steps
 - Digital programmable controls: Time, Temperature, Humidity
 - Heat settings from 175°-500° F
 - Saves up to 99 programs including 12 "Quick Access" programs
 - Handles 3 half size sheet pans (not included)
 - 3 wire shelves included
 - Cooking chamber: 10-1/4" H x 19-1/4" W x 14" D (1.6 cu. ft.)
 - 10 hour timer or continuous on
 - Light flashes and unit beeps at end of cycle
 - Heavy duty stainless steel construction
 - Heavy duty door & hinge construction
 - Extra large motor for long lasting use
 - 2-5/8" between shelves
 - 1 fan; 2 fan speeds
 - Interior LED light
 - Auto shut off when door is opened
 - Includes electro valve for direct plumbed water connection
 - "Cool-touch" double wall glass door
 - Stackable with optional XWKQT-00HS-E Stacking Kit
 - NSF; MET to UL & CSA Standards/ listed by UNOX S.p.A.
 - Energy Star rated
 - Chef Support - via phone
 - 2 year Limited Warranty (one year On-site service & parts, 2nd year parts only)**
 - **90 day warranty on light bulbs & gasket (not service center items); 30 days on glass; one year on motor
 - 208-240 Volts / 3300 Watts / 14 Amps / Single Phase / 60Hz
 - NEMA 6-20P Plug
 - Freight class 200 NOTE: This model must ship by truck, not UPS
- OPTIONAL ACCESSORIES:**
- XAKPT-08HS-C Proofer
 - XAKHT-HCHS Ventless Hood
 - XWKQT-00HS-E Stacking Kit
 - Stands: OST-34A-C, OST-34A-CS
 - Heavy-Duty 2-Oven Stand: OV-HDS

Model	Color	Volts	Watts	Amps	Unit Dimensions	Unit Wt.	Ship Wt.	Carton Dimensions	Cube	UPC#
XAFT-03HS-LD	Stainless	208-240	3300	14	w:23 ⁵ / ₈ ", h:16 ⁵ / ₈ ", d:29"	85 lbs.	130* lbs.	w:42", h:23", d:48"*	26.8*	654796-55130-9

*includes dimensions & weight (approx. 40 lbs.) of shipping skid

For more information, please contact Cadco, Ltd, 200 International Way, Winsted, CT 06098
Tel. (860)738-2500 • Fax (860) 738-9772 • E-mail: info@cadco-ltd.com • Web site: cadco-ltd.com