



BOXER

FLUSH MOUNT CEILING

location:
DAMP

SPECIFICATIONS:

DESCRIPTION

The low profile Boxer flush mount uses a multi-layered glass, with two softly radiused square sections fused onto a flat opti-white glass. The upper portion is opal with a contemporary polished finish, and the lower section is an elegant clear blown glass. The tranquil glow has a low-key harmonious display that exudes warmth, and when lit the stylish glass becomes truly vitalizing.

LAMPING

LED: 30W Integrated source, 120V, CL dimmable, 90+ CRI, 3000°K CCT, 2600 lumens, 30,000 hours, included.

DIFFUSER

Handcrafted glass diffuser in Opal Glossy with clear or smoke stone trim. 12" Dia. x 3" H

CONSTRUCTION

Stamped aluminum fitter is powder coated white.

MOUNTING


Installs directly to a 4" octagonal outlet box, centered on fixture. 90°C supply wire required for incandescent lamping.

LABELS

UL or ETL Listed. Suitable for Damp Locations (interior use only).



OPAL GLOSSY/CLEAR (BOXERCLC-LED)



BOXERSMC-LED
OPAL GLOSSY/SMOKE



ORDERING:

FIXTURE/DECOR	-	LAMP OPTIONS
BOXERCLC Opal Glossy/Clear		LED 30W LED 120V,
BOXERSMC Opal Glossy/Smoke		2600 lumens
		3000K

Ex. BOXERSMC-LED
Boxer Ceiling w/ Opal Glossy/Smoke Glass

Project Information:

All dimensions provided are nominal.
Allowance must be made for dimensional tolerance in handcrafted glasses.

REV 1/22