

PAHU 4

VANITIES WALL

SPECIFICATIONS:

DESCRIPTION

2-4 light vanity luminaires featuring handcrafted glass.

LAMPING

Standard: 40W Low-pressure G9 Halogen, 120V, lamp included. Suitable for use in an open fixture. Dimmable with standard incandescent dimmer (not included). **LED:** 5W Replaceable source, 120V, dimmable, 90+ CRI, 3000° K CCT, 450 lumens, 25,000 hours, lamp included.

DIFFUSER

Shade shall be handcrafted double glass of various decors. Outer diameter of 4.0" and height of 7.0", spaced 7.875" apart on center.

CONSTRUCTION

Fixture utilizes metal arm assembly and stamped steel body, with plated finish. Decorative finials can be removed for downlighting applications. Decorative outlet box cover optional when not required.

METAL FINISH

Fixture shall be finished in Bronze, Chrome or Satin Nickel.

MOUNTING

Installs directly to a 4" octagonal outlet box, with 1.75" left or right offset. Canopy allows direct wiring without outlet box, where armored cable or non-metallic sheathed cable is employed, and the decorative outlet box cover is not required. Orient upward or downward, wall-mount only.

LABELS

UL or ETL Listed. Suitable for Damp Locations (interior use only).



PAHU 4 SHOWN IN CLEAR/OPAL (C44007) WITH SQUARE CANOPY



For ordering information, see next page

All dimensions provided are nominal. Allowance must be made for dimensional tolerance in handcrafted glasses. location:




ORDERING:

FIXTURE -	GLASS OPTIONS	- METAL FINISH	- METAL FINISH ·	OPTIONS
2SW 2 Light Vanity	A44007 Trans. Amethyst/Opal	(blank) 40W G9 Hal	BR Bronze	SQ Square
3SW 3 Light Vanity	C44007 Clear/Opal	LED 5W LED 120V,	CR Chrome	Canopy
4SW 4 Light Vanity	G44007 Trans. Armagnac/Opal L44007 Trans. Olive/Opal S44007 Trans. Smoke/Opal	dimmable	SN Satin Nickel	

Ex. 3SW-G44007-SN

Pahu 4 3-Light Vanity w/ Trans. Armagnac/Opal Glass, Satin Nickel Finish











Canopy allows direct wiring without outlet box, where armored cable or non-metallic sheathed cable is employed, and the decorative outlet box cover is not required. Orient upward or downward, wall-mount only.

Project Information: