# POGO

SEMI-FLUSH MOUNT CELLING

location:

# **SPECIFICATIONS:**

#### **DESCRIPTION**

Semi-flush mounted ceiling fixture, featuring handcrafted radiused drum-shaped glass.

## **LAMPING**

**Standard:** 3x60W A19 120V incandescent, lamp not included. Dimmable with standard incandescent dimmer (not included).

**LED:** 28W Integrated source, 120V, CL dimmable, 90+ CRI, 3000°K CCT, 2160 lumens, 30,000 hours, included.

### **DIFFUSER**

Handcrafted glass shade with inner foil in various decors with lamp shield, which can be removed for exposed lamp appearance. 16'' Dia. x 8'' H

#### CONSTRUCTION


Canopy (5" dia.) is plated stamped steel. Canopy and glass retainer hardware are available in either Bronze or Satin Nickel finish.

#### MOUNTING

Installs directly to a 4" octagonal outlet box, centered on fixture. 90°C supply wire required for incandescent lamping.

#### IARFIS

UL or ETL Listed. Suitable for Damp Locations (interior use only).





BLACK/INNER GOLD FOIL (POGOGF)

POGOGG GOLD'INNER GOLD FOIL

POGOSF WHITE/INNER SILVER FOIL

POGOSS SILVER/INNER SILVER FOIL







## **ORDERING:**

Project Information:

FIXTURE -	SHADE OPTIONS	- LAMP OPTIONS	- METAL FINISH
1KM Flat Canopy	POGOGG Gold/Inner Gold Foil	(blank) 3x 60W Incan	BR Bronze
	POGOGF Black/Inner Gold Foil	LED 28W LED,	SN Satin Nickel
	POGOSF White/Inner Silver Foil	2160 lumens	
	POGOSS Silver/Inner Silver Foil		

Ex. 1KM-POGOSF-SN

Pogo Ceiling, White/ Inner Silver Foil, Satin Nickel Finish

All dimensions provided are nominal.
Allowance must be made for dimensional tolerance in handcrafted glasses.

**REV 12/18**