

TORRE 22



WALL SCONCES

location: DAMP

SPECIFICATIONS:

DESCRIPTION

Wall-mounted ADA-compliant sconce featuring open-ended handcrafted glass.

LAMPING

Standard: 2x 100W A19 120V incandescent, suitable for dimming, lamp not included. (*Incandescent dimmer is suitable for dimming, not included*) **LED:** 11W LED Replaceable source 120V, CL dimmable, 90+ CRI, 3000°K CCT, 1100 lumens, 30,000 hours, lamp included.

DIFFUSER

Diffuser shall be handcrafted glass of various decors.

CONSTRUCTION

Glass is secured to the backplate by decorative thumbscrews. Rectangular backplate (nominal 4"W x 17.25" H) shall be constructed of steel, powder-coated white.

METAL FINISH

Decorative metal accents shall be in various finish options.

MOUNTING


Installs directly to a 4" octagonal outlet box. 75°C supply wire required for incandescent lamping. Top of glass is approximately 10.875" above the outlet box centerline.

LABELS

UL or ETL Listed. Suitable for Damp Locations (interior use only).



TORRE 22 SHOWN IN WHITE (819407) & SILVER FOIL (8194SF)





For ordering information, see next page

All dimensions provided are nominal.
Allowance must be made for dimensional tolerance in handcrafted glasses.





ORDERING:

FIXTUE	RE/DECOR	- LA	MP OPTIONS	- METAL FINISH -		- OPTIONS		
819407	White	(blank)	2x 100W A19 Incan	7	BK	Black	LW	Low
8194CF	Copper Foil	LED	2x 11W LED 120V,	- 1	BR	Bronze		Wattage
8194CH	Cherry		dimmable		PN	Polished Nickel		labeling
8194GF	Gold Foil				SN	Satin Nickel		
8194KR	Chalk			V	۷H	White		
81940K	0ak							
8194SF	Silver Foil							
8194TN	Titan							

Ex. 8194CH-SN

Torre 22 Wall Sconce w/ Cherry Glass, Satin Nickel Finish

Project Information:		