

Project:	AIA#
Item:	
Location:	SIS#
Approved:	

SM SCHOOL MILK COOLERS

SM34HC Single Access, Cold Wall Hydrocarbon Series

MODELS: SM34HC-S SM34HC-W



SM34HC-S



OPTIONS & ACCESSORIES

- Wrap around & corner bumpers
- Graphics

3 Year Parts/Labor Warranty Additional 2 Year Compressor Warranty

CABINET CONSTRUCTION

- SS units: Stainless steel exterior and interior
- White units: White coated steel exterior and interior is galvanized steel with stainless steel floor for maximum milk crate support.
- Lids, doors, adjustable hinges and door latches made from stainless steel are standard on all units
- Full electronic Control
- Heavy-duty epoxy coated steel wire floor racks standard
- Floor drain is centrally located for easy cleaning, connecting to drain hose with hose adapter
- Flexible compression door gaskets ensure tight seal
- Self-latching doors/lids with safety bumpers
- Exterior thermometer
- Cylinder lock
- 4" Heavy-duty plate casters (2 with locks)
- Maintains continuous milk temperature between 36° 38°F

REFRIGERATION SYSTEM

- Refrigeration system uses R290 refrigerant to comply with all environmental concerns
- Automatic, non-electric defrost
- Epoxy coated evaporator coil


















MODEL	SM34HC-S	SM34HC-W
EXTERNAL DIMENSIONAL DATA		
Width Overall	34"	34"
Depth Overall	30 5/8"	30 5/8"
Height Overall with Casters	41 1/8"	41 1/8"
Number of Lids/Doors	Single Access	Single Access
INTERNAL DIMENSIONAL DATA		
NET Capacity (cubic ft.)	12.73	12.73
Internal Width Overall (in)	31"	31"
Internal Depth Overall (in)	27"	27"
Internal Height Overall (in)	25 3/4"	25 3/4"
CASE CAPACITIES		
13" x 13" x 11"	8	8
19" x 13" x 11"	4	4
ELECTRICAL DATA		
Full Load Amperes 115/60/1	2.2	2.2
REFRIGERATION DATA		
Horsepower	1/3	1/3
Capacity BTU	1224	1224
WEIGHT DATA		
Gross Weight (Crated lbs)	277 lbs	277 lbs
Height - Crated	47"	47"
Width - Crated	37"	37"
Depth - Crated	34"	34"

SM Series—School Milk Cooler

Models: SM34HC-S, SM34HC-W



ELECTRICAL CONNECTION

















Units pre-wired at factory and include 8' long cord and plug set.



