

70622

Wall-/Floor Washing Brush, 18.5", Stiff, Green



This large washing Brush is great for cleaning all types of floor surfaces, including epoxy, tiles and cement. Can be used with any Vikan handle.

Technical Data

Item Number	70622
Bristle stiffness	Stiff
Visible bristle length	1.7 "
Material	Polypropylene Polyester (PBT) Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Complies with EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
Complies with FDA Regulation I CFR 21¹	Yes
Complies with UK 2019 No. 704 on food contact materials	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Complies with California Proposition 65	Yes
Complies with Halal and Kosher	Yes
PFAS, Phthalates and BPA intentionally added	No
Box Quantity	8 Pcs.
Quantity per Pallet (80 x 120 x 180-200 cm)	384 Pcs.
Quantity Per Layer (Pallet)	48 Pcs.
Box Length	20.1 "
Box Width	11.8 "
Box Height	8.3 "
Length	18.5 "
Width	3.1 "
Height	4.5 "
Net Weight	1.9621 lbs
Weight bag (Recycling Symbol "4" Low Density Polyethylene (LDPE))	0.02 lbs
Weight cardboard (Recycling symbol "20" PAP)	0.08 lbs
Tare Total	0.1 lbs
Gross Weight	2.0591 lbs
Cubic Feet	0.1528 ft ³
Recommended sterilisation temperature (Autoclave)	249.8 °F
Max. cleaning temperature (Dishwasher)	199.4 °F
Max usage temperature (food contact)	176 °F
Max usage temperature (non food contact)	212 °F
Min. usage temperature	-4 °F
Max. drying temperature	212 °F
Min. pH-value in usage concentration	2 pH

Max. pH-value in Usage Concentration	10.5 pH
GTIN-13 Number	5705020706226
GTIN-14 Number (Box quantity)	15705020706223
Customs Tariff No.	96039099
Country of Origin	Denmark

New equipment should be cleaned, disinfected, sterilized, and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 32 °Fahrenheit.