

Miller Falcon 16 ft. and 20 ft. SRL

Description

Miller Falcon 16ft (4.9m) and 20ft. (6.1m) web lifelines with high impact-resistant nylon housing withstands the harsh rigors of the toughest applications. Pound for pound the strongest, most durable line of self-retracting lifelines on the market.


Materials

Housing: High impact-resistant nylon
Lifeline: .69 in. (17.5 mm) wide
Core: Technora® (aramid fiber)
Outer cover: Chemically treated polyester for increased abrasion resistance

Snap Hook: Galvanized, zinc-plated steel or aluminum
Carabiner: Galvanized, zinc-plated steel or aluminum
Hub: Aluminum
Braking Mechanism: Aluminum

Technical

Max. Working Load: 400 lbs. (181.4 kg)
Working Length: 16 ft. (4.9 m)
20 ft. (6.1 m)
Max. Arrest Distance: 54 in.
(when tested to ANSI Z359.14)
Avg. Arresting Force: 900 lbs. (4 kN)
(when tested to ANSI Z359.14)
Max. Peak Arresting Force: 1,800 lbs. (8kN)
(when tested to ANSI Z359.14)
Unit Minimum Ultimate Strength: 3,000 lbs. (13.34 kN)



Certification

Meets all applicable OSHA 1926.502, ANSI A10.32, ANSI Z359.14 Class B and CSA Z259.2.2 requirements..

Model Number	Length	Unit Connector	Lanyard Connector	Weight
MP16P-1-Z7/16FT	16' (4.9 m)	Aluminum Twist- Lock Carabiner	Aluminum Locking Snap Hook	3.0 lbs. (1.36 kg)
MP20P-1-Z7/20FT	20' (6.1 m)	Aluminum Twist- Lock Carabiner	Aluminum Locking Snap Hook	3.2 lbs. (1.45 kg)
MP16P-Z7/16FT	16' (4.9 m)	Steel Twist-Lock Carabiner	Steel Locking Snap Hook	4.1 lbs. (1.86 kg)
MP20P-Z7/20FT	20' (6.1 m)	Steel Twist-Lock Carabiner	Steel Locking Snap Hook	4.2 lbs. (1.90 kg)

Limitless Possibilities. Ask the Expert.

Technical Service: 800.873.5242
www.millerfallprotection.com

Honeywell Industrial Safety

900 Douglas Pike
Smithfield, RI 02917

USA

Phone: 800.430.5490
Fax: 800.322.1330

Canada

Phone: 888.212.7233
Fax: 888.667.8477

! This equipment should only be used after reading and understanding the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.