



SKU # 9005-8K-G5-CANBUS

Part # 1000616

Description

9005 GEN5 Canbus HID Conversion Headlight Kit - 55-watt SUPER SLIM Ballast Kit

Categories HID & LED Headlights, HID Headlight Conversions

Sub-Categories HID Conversion Kits, Gen5 CANBUS HID Headlight Kit

UPC 811712028417

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Gen5 CANBUS HID Kit - 8K

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

55-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

8,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

Beam Pattern

N/A



Product Information

The most powerful CANBUS kit on the market Race Sport Lighting's Gen5 55W Canbus HID Kit boasts a pair of 55W HID ballasts, the most powerful canbus kit in our lineup. • 3 Year Warranty • SLIM weatherproof design • Error light prevention circuitry built in • RF interference prevention circuitry built in • High quality igniter system • 55W ballast power • Oriented for CANBUS vehicles model year 2005 and newer • Kit includes: -(2) 55W CANBUS Ballasts -(2) 55W HID Bulbs -Hardware -Instruction Card • Bi-xenon kits include high/low control pack harness

Est. Labor

Hours

Gross Weight

6.20

Width

6.00

Net Weight

6.00

Height

10.00

DIM Weight

6.04

Depth

14.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com