



SKU # 9006-3K-GEN6

Part # 1000701

Description

9005 3K GEN6 Professional Grade Canbus HID SLIM Ballast 99% Plug-&-Play Kit



Categories HID & LED Headlights, HID Headlight Conversions

Sub-Categories HID Conversion Kits, Gen6 CANBUS HID Headlight Kit

UPC 887753753892

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Gen6 CANBUS HID Kit - 3K

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Product Information

Race Sport Lighting has done it again. 100% Plug-&-Play on most vehicles, no additional interface harnesses on single beam setups. You asked and we have built it, designed to meet the needs of today's most complicated vehicles, Race Sport Lighting brings you their Generation 6 CANBUS ballasts. Features • Direct Canbus communication • No radio interference • Built in error light eliminator • Heavy duty cables with braided sleeves • Lifetime Warranty (on ballasts, 1 year warranty on bulbs) • Plug-&-Play interfacing on single beam for Mopar and others Specifications • 9-16v • 2.7A • 35W

Est. Labor

Hours

Gross Weight

3.20

Width

7.50

Net Weight

3.20

Height

3.75

DIM Weight

2.02

Depth

10.00

Kelvin (ColorTemperature)

3,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

Lifetime

Lumens

Beam Pattern

N/A

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov