



SKU # 9007CARGB

Part # 1001054

Description

V1 Sale - 9007 Demon Eye® LED Headlight Conversion Kits - Dual Function Kit with driving and accent functions

Categories HID & LED Headlights, LED Headlight Conversions

Sub-Categories LED Conversion Kits, DemonEYE LED Headlight Kits

UPC 817999021646

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Demon Eye LED Headlight Kit

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

12VDC

Current Draw

3A

Wattage

35-Watts

Chip Type

COB

IP Rating

IP67

LUX

2,000 LUX



Product Information

Race Sport Lighting DemonEYE LED Headlight Kit



Race Sport Lighting's DemonEYE LED Accent Headlight kit gives you a fully functional 2,000 LUX headlight or fog light as well as attractive multi-color accent lighting.

The DemonEYE kit features our ColorSMART Bluetooth Technology. Which allows you to control the color and accent pattern from your smart phone or Bluetooth-enabled device.

www.racesportinc.com

Whether on the road using the full functional headlight or at the show using the multi-color accent DemonEYE's are a game changer!

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

4,800lm

**Beam
Pattern**

N/A

• 2,000 Lux

• 6,500 Kelvin Color Temperature

• 1 Year Warranty

Est. Labor

Hours

Gross Weight

1.00

Width

8.25

Net Weight

1.00

Height

2.50

DIM Weight

1.19

Depth

8.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov