



SKU # H10-12K-G1-CANBUS-R

Part # 1002597

Description

H10 GEN 1® Canbus HID Mid-Slim Ballast Kit w/ Relay Resistor Harness



Categories HID & LED Headlights, HID Headlight Conversions

Sub-Categories HID Conversion Kits, Gen1 CANBUS HID Headlight Kit

UPC 887753758002

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Gen1 CANBUS HID Kit - 12K

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID

12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Product Information

Bulletproof quality that lasts the life of the vehicle • 3 Year Warranty • MID-SLIM weatherproof design • High quality igniter system • 35W ballast power • Oriented for CANBUS vehicles model year 2005 and newer • Kit includes: -(2) 35W CANBUS Ballasts -(2) 35W HID Bulbs -(1) Relay Resistor Harness -Hardware -Instruction Card • Bi-xenon kits include high/low control pack harness

Est. Labor

Hours

Gross Weight

2.00

Width

8.00

Net Weight

2.00

Height

2.00

DIM Weight

1.15

Depth

10.00

Kelvin (ColorTemperature)

12,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

Beam Pattern

N/A

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov