



## SKU # H15D-10K-SLIM

Part # 1003139

### Description

H15 HID Digital Super-Slim Ballast Kit

**Categories** HID & LED Headlights, HID Headlight Conversions

**Sub-Categories** HID Conversion Kits, D-Elite HID Headlight Kit

**UPC** 887753759894

**Unit of Measure** Kit

**Related Skus:**

**Cross Sell Skus:**

### Condition

New

### Manufacturer

Race Sport Lighting

### EZ Category

DC Slim HID Kit - 10K

### Harmonization Code

8512.20.2080

### Universal

YES

### Life Expectancy

10,000 hours

### SEMA Product

Headlight Conversion Kit

**Part Type ID** 12571

### Reverse Polarity

Headlight Conversion Kit

### Operating Voltage

### Current Draw

### Wattage

35-Watts

### Chip Type

XENON HID

### IP Rating

IP67

### LUX

### Est. Labor

Hours

### Gross Weight

2.00

### Width

8.00

### Net Weight

2.00

### Height

2.00

### DIM Weight

1.15

### Depth

10.00

### Kelvin (ColorTemperature)

10,000K

### Universal or Vehicle Specific

Universal

### Made In

China

### Warranty

1 year

### Lumens

### Beam Pattern

N/A



### Product Information

Economically Priced SLIM DC Technology Kits • 12 Month Warranty • SMT Technology • High quality igniter system • 35W ballast power • SLIM weatherproof design • Kit includes: -(2) 35W Ballasts -(2) 35W HID Bulbs -Hardware - Instruction Card • Bi-xenon kits include high/low control pack harness

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)