



SKU # H15-10K-G2-CANBUS

Part # 1003082

Description

H15 GEN 2® Canbus HID Regular Ballast Kit

Categories HID Headlight Conversions

Sub-Categories Other HID Conversion Kits

UPC 887753759399

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Gen2 CANBUS HID Kit - 10K

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Est. Labor

Hours

Gross Weight

2.00

Width

8.00

Net Weight

2.00

Height

2.00

DIM Weight

1.15

Depth

10.00

Kelvin (ColorTemperature)

10,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

2 year

Lumens

Beam Pattern

N/A



Product Information

CANBUS quality at affordable prices • 2 Year Warranty • High quality igniter system • 35W ballast power • Oriented for CANBUS vehicles model year 2005 and newer • Kit includes: -(2) 35W CANBUS Ballasts -(2) 35W HID Bulbs - Hardware -Instruction Card • Bi-xenon kits include high/low control pack harness

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com