



SKU # H3TLED

Part # 1006707

Description

Terminator Series H3 Fan-less LED Conversion Headlight Kit with Pin Point Projection Optical Aims and Shallow Mount Design

Categories HID & LED Headlights, LED Headlight Conversions, Powersports

Sub-Categories LED Conversion Kits, Terminator LED Headlight Kits,

UPC 817999024050

Unit of Measure Kit

Related Skus:

RSCAS001

Cross Sell Skus:

RSKIT,RSUKIT,RS8PRGBW

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Terminator LED Headlight Kits

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

12VDC

Current Draw

3.6 Amps

Wattage

50-Watts

Chip Type

PHILLIPS

IP Rating

IP67

LUX

5,614 RAW LUX

Kelvin (ColorTemperature)

6,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

2 year

Lumens

4,748 RAW LUMENS

Beam Pattern

N/A



Product Information

The TERMINATOR™ LED Kit is world famous for its superior performance when compared to other LED lights on the marketplace. We use an incredible high performing reflector to focus the light and keep the light forward where it needs to be. This kit boasts just over 2,000LUX per bulb / 4,000LUX per kit in our lab, making it the perfect high output bulb for any vehicle type. Its shallow mount fan-less design keep the bulb from overheating and delivering consistent performance day after day. • See 2-3 times further than stock lighting systems, increasing stopping distance by 200% • LED technology provides instant on/off light with no ramp-up time • Fanless heat-sink technology • Low mounting depth base design • LED lasts longer than your OEM lighting systems • Focus cup design for narrow projection beam - no glare • Plug-n-play design for easy installation (additional interface harnesses may be required for some vehicles) • 2 Year Warranty • Rated 2,000 LUX/bulb or 4,

Est. Labor 0.5 Hours

Gross Weight 0.65 **Width** 6.25

Net Weight 0.65 **Height** 2.25

DIM Weight 0.58 **Depth** 5.75